



**NOTES:**


1. SUBSTRATE: CALCIUM FLUORIDE (CaF<sub>2</sub>)
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: NONE  
S2: NONE
3. DESIGN WAVELENGTH: 5 μm
4. FOCAL LENGTH TOLERANCE: ±2 @ DWL
5. RoHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY**

REV. A	S1 & S2
SHAPE	CONVEX
RADIUS	79.07
SURFACE QUALITY	60-40
CLEAR APERTURE	90%
BEVEL MAX	PROTECTIVE AS NEEDED

EFL @ 5μm	100	 <b>Edmund Optics<sup>®</sup></b>	
BFL @ 5μm	98.36		
THIRD ANGLE PROJECTION		TITLE	25.4mm DIAMETER X 100mm FL, CaF <sub>2</sub> DOUBLE-CONVEX LENS
ALL DIMS IN	mm	DWG NO	47059
			SHEET 1 OF 1