


NOTES:

1. SUBSTRATE:  
N-BK7
2. COATING (APPLY ACROSS COATING APERTURE)  
S1: ALUMINUM WITH PROTECTED OVERCOAT  
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE

3. FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	1.26 x 0.9	0.9 x 0.9
COATING APERTURE	1.26 x 0.9	0.9 x 0.9
SURFACE FLATNESS	$\lambda/4$	$\lambda/4$
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION



ALL DIMS IN

mm

TITLE	1mm, Aluminum Coated, N-BK7 Right Angle Prism
DWG NO	86621
SHEET 1 OF 1	