
NOTES:


- 1. SUBSTRATE: UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS COATING APERTURE) \$1 & \$2: RAB\$ ≤0.25% @ 880nm RAVG ≤1.25% @ 400 - 870nm RAVG ≤1.25% @ 890 - 1000nm
- 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN <5 ARCSEC

4.\ FINE GRIND SURFACE

5. Rohs Compliant



ALL DIMS IN



PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	20-10	20-10	
CLEAR APERTURE	Ø40.00	Ø40.00	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

			Edmund Opt			
	THIRD ANGLE_ PROJECTION	$\phi \Box$	TITLE	50mm DIA., 5mm THICK, VIS-NIR COATE FUSED SILICA WINDOW	50mm DIA., 5mm THICK, VIS-NIR COATED λ/10 FUSED SILICA WINDOW	
-	ALL DIMS IN	mm	DWG NO	0.4450	SHEET	

84458

DWG NO