

NOTES:

1. SUBSTRATE MATERIAL:
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2:
LASER V-COAT

R(abs) <0.25% @ 1064nm

 3. FINE GROUND SURFACE


4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			 Edmund Optics®		
SHAPE	CONVEX	PLANO	EFL	100±3%			
RADIUS	51.68	∞	BFL	(98.68)			
SURFACE QUALITY	60-40	60-40			12.5mm DIA X 100.0mm FL 1064nm V-COAT, CYLINDER LENS		
CLEAR APERTURE	∅ 11.50	∅ 11.50					
COATING APERTURE	∅ 11.50	∅ 11.50	ALL DIMS IN mm		DWG NO 33234		
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					SHEET 1 OF 1