




NOTES:

1. SUBSTRATE:
D-ZLAF52LA
2. NUMERICAL APERTURE:
OBJECT: 0.26
IMAGE: 0.52
WD, IMAGE(mm): 7.09
3. COATING
S1 & S2: R(AVG) $\leq 0.5\%$ @ 350 - 700nm
4. FOCAL LENGTH TOLERANCE: $\pm 1\%$
5. TRANSMITTED WAVEFRONT ERROR (λ , RMS): < 0.200
6. MAGNIFICATION: 2X



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	2.76	 Edmund Optics®		
SHAPE	CONVEX	CONVEX	BFL	2.70			
SURFACE QUALITY	40-20	40-20	THIRD ANGLE PROJECTION 	TITLE	0.52 NA 2.76mm FL 350-700nm AR COATED, MOLDED ASPHERIC LENS		
CLEAR APERTURE	$\phi 4.12$	$\phi 4.12$					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	87133	SHEET 1 OF 1