



NOTES:

1. SUBSTRATE:
D-ZLAF52LA
2. NUMERICAL APERTURE: 0.4
3. COATING
S1 & S2: R(AVG) ≤ 0.5% @ 350 - 700nm
4. FOCAL LENGTH TOLERANCE: ±1%
5. TRANSMITTED WAVEFRONT ERROR (λ, RMS): < 0.070



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	6.24	 Edmund Optics®	0.40 NA 6.24mm FL 350-700nm AR COATED, MOLDED ASPHERIC LENS	
SHAPE	CONVEX	PLANO	BFL	3.46			
SURFACE QUALITY	40-20	40-20	THIRD ANGLE PROJECTION		TITLE	DWG NO 87125	
CLEAR APERTURE	Ø5.00	Ø5.00	ALL DIMS IN	mm			
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				SHEET 1 OF 1	