


NOTES:

- 1. SUBSTRATE:  
D-ZK3
- 2. NUMERICAL APERTURE: 0.55
- 3. COATING  
S1 & S2: R(AVG) ≤ 0.5% @ 350 - 700nm
- 4. FOCAL LENGTH TOLERANCE: ±1%
- 5. TRANSMITTED WAVEFRONT ERROR (λ, RMS): < 0.087



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	4.60	 <b>Edmund Optics®</b>		
			BFL	2.71			
SHAPE	CONVEX	PLANO		TITLE	0.55 NA 4.60mm FL 350-700nm AR COATED, MOLDED ASPHERIC LENS		
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø4.80	Ø4.80					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	87157	SHEET 1 OF 1