



NOTES:

1. SUBSTRATE MATERIAL:  
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2:  
NIR I  
 $R(AVG) \leq 0.5\%$  FROM 600-1050nm @ 0° AOI

3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
5. FOCAL LENGTH TOLERANCE:  $\pm 1\%$
6. PLANO AXIS WEDGE TOLERANCE:  $< 5$  ARCMIN  
POWER AXIS WEDGE TOLERANCE:  $< 5$  ARCMIN
7. RoHS COMPLIANT





SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

REV. A	S1	S2
SHAPE	CONCAVE	PLANO
RADIUS	25.84	$\infty$
SURFACE QUALITY	40 - 20	40 - 20
CLEAR APERTURE	$\varnothing 22.86$	$\varnothing 22.86$
COATING APERTURE	$\varnothing 22.86$	$\varnothing 22.86$
POWER AT 632.8nm	1.5 WAVES PV	1.5 WAVES PV
IRREGULARITY AT 632.8nm	0.25 WAVE PV	0.25 WAVE PV
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

EFL	(-50)mm	 <b>Edmund Optics®</b>		
BFL	(-51.978)mm			
	TITLE	LENS CYL SHAPING 25.4mm DIA. X -50mm FL NIR I		
		DWG NO	34683	SHEET 1 OF 1
ALL DIMS IN	mm			