




NOTES:

- 1. SUBSTRATE:
D-ZK3
- 2. NUMERICAL APERTURE: 0.56
- 3. COATING
S1 & S2: R(ABS) < 1.0% @ 600 - 1050nm
- 4. FOCAL LENGTH TOLERANCE: ±1%
- 5. TRANSMITTED WAVEFRONT ERROR (λ, RMS): < 0.071



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY			EFL	5.50	 Edmund Optics®		
	S1	S2	BFL	3.73			
SHAPE	CONVEX	PLANO			TITLE	0.56 NA 5.50mm FL 600-1050nm AR COATED, MOLDED ASPHERIC LENS	
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø6.00	Ø6.00			DWG NO	87146	
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					
			ALL DIMS IN	mm			
					SHEET 1 OF 1		