


NOTES:

1. SUBSTRATE MATERIAL:  
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1 & S2: NIR I  
  
R(avg)  $\leq 0.5\%$  @ 600 - 1050nm



3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div>EFL-12.5</div> <div>BFL-13.46</div> <div><div><div></div><div></div></div><div>Edmund Optics®</div></div>			
SHAPE	CONVEX	PLANO				
RADIUS	-6.48	∞	<div>THIRD ANGLE PROJECTION</div> <div><div></div><div></div></div> <div>TITLE</div> <div>6.25mm DIA X -12.5mm FL NIR I COATED, CYLINDER LENS</div>			
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	Ø 5.25	Ø 5.25	<div>ALL DIMS IN</div> <div>mm</div> <div>DWG NO</div> <div>69811</div> <div>SHEET 1 OF 1</div>			
COATING APERTURE	Ø 5.25	Ø 5.25				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				