




NOTES:

- S2 & S3: NONE


4. ELEMENTS TO BE CEMENTED WITH NOA61

9. CENTERING TOLERANCE AFTER CEMENTING:
IMAGE RUNOUT: 0.1mm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

		ELEMENT A		ELEMENT B		SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY			
REV. A		S1	S2	S3	S4	EFL	25	 Edmund Optics®	
SHAPE		CONVEX	CONVEX	CONCAVE	CONVEX	BFL	18.23		
RADIUS		10.55	10.55	10.55	200.14			TITLE 12.5mm DIA. X 25mm FL, ACHROMATIC CYLINDER LENS	
SURFACE QUALITY		40-20	40-20	40-20	40-20				
CLEAR APERTURE		Ø11.50	Ø11.50	Ø11.50	Ø11.50	ALL DIMS IN		mm	
COATING APERTURE		Ø11.50	N/A	N/A	Ø11.50				
BEVEL		PROTECTED AS NEEDED				DWG NO		SHEET 1 OF 1	