TECHSPEC® Vega[™] Nd:YAG Laser Line Beam Expanders 1064nm • 3X #35-099


- λ/10 Transmitted Wavefront Error
- Fused Silica Substrate Offers Excellent Price and Performance
- Divergence Adjustment to Compensate for Input Beam Divergence
- TECHSPEC® Vega™ Broadband Beam Expanders Also Available


TECHSPEC® Vega™ Nd:YAG Laser Line Beam Expanders are designed for demanding laser applications including laser materials processing, medical, and research. These compact beam expanders are optimized at Nd:YAG wavelengths for high performance transmitted wavefront, with most designs achieving better than $\lambda/10$ transmitted wavefront error. TECHSPEC® Vega™ Nd:YAG Laser Line Beam Expanders easily mount with M30 x 1 threading and provide excellent value both for single unit purchases as well as volume integration.

	1
Design Wavelength (DWL):	1064nm
Magnification:	3X
Maximum Input Aperture (mm):	10
Divergence Adjustable:	✓
Maximum Output Aperture (mm):	23mm
Length (Without Threads):	81.1mm
Housing Outer Diameter (mm):	29.95mm
Weight:	76g
Damage Threshold:	10 J/cm² at 1064nm at 10ns at 20Hz
Transmission @ DWL:	>99 (nominal)
Lens Material:	UV Fused Silica
*Mounting Thread:	M30 x 1









For more cost sensitive applications that don't require divergence adjustment, see our Scorpii™ Nd:YAG Beam expanders. For applications that require sliding optics or larger input apertures, please see our Draconis™ Nd:YAG Laser Line Beam Expanders.

