




NOTES:

1. SUBSTRATE MATERIAL:  
ALUMINUM
2. FINISH (EXCEPT SURFACE S1):  
BLACK ANODIZED
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: PROTECTED ALUMINUM  
R(AVG) >85% from 0.4-0.7 $\mu$ m  
R(AVG) >97% from 2 - 12 $\mu$ m  
  
SURFACE ROUGHNESS: <100 Å RMS
4. FOCAL LENGTH TOLERANCE:  $\pm$ 1%
5. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	EFL	76.20			<b>Edmund Optics®</b>	
SHAPE	PARABOLIC	PFL	38.10				
REFLECTIVE WAVEFRONT DISTORTION AT 632.8nm (RMS)	3/2 $\lambda$	THIRD ANGLE PROJECTION		TITLE	$\varnothing$ 76.2 X 76.2mm EFL 90° OAP PROTECTED ALUMINUM MIRROR 100Å		
SURFACE FIGURE AT 632.8nm (RMS)	3/4 $\lambda$	ALL DIMS IN	mm	DWG NO	35522	SHEET 1 OF 1	
CLEAR APERTURE	90%						
BEVEL	PROTECTIVE AS NEEDED						