




NOTES:

1. SUBSTRATE MATERIAL:
ZINC SELENIDE (ZNSE)
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1:
50/50 ± 25% @ 2 - 20µm

S2:
AR COATING
3. RoHS COMPLIANT
4.  GROUND SURFACE




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	3λ/4	3λ/4
CLEAR APERTURE	Ø45.00	Ø45.00

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

TITLE	50mm Diameter, 2-20µm Zinc Selenide IR Plate Beamsplitter	
DWG NO	36659	SHEET 1 OF 1