


- NOTES:
- 1. COATING (APPLY ACROSS CLEAR APERTURE)
LASER V-COAT
 $R(ABS) \leq 0.25\% @ 532nm$
 - 2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD (PULSED)	5J/cm ² @ 10ns, 20Hz, 532nm
DESIGN WAVELENGTH DWL (nm)	532
EXPANSION POWER	7X
TRANSMISSION (%)	> 99 (NOMINAL)
NOMINAL PERFORMANCE	< λ /10 FOR 3.6mm INPUT BEAM (NOMINAL)

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 Edmund Optics®			
TITLE	7X 532nm VEGA™ Nd:YAG LASER LINE BEAM EXPANDER		
DWG NO	35112	SHEET 1 OF 1	