


NOTES:

1. SUBSTRATE:  
BK-7
2. CENTERING TOLERANCE (AT 587.6nm):  
BEAM DEVIATION (HALF ANGLE): <6 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)  
S1: NONE  
S2: NONE


4. FINE GRINDE SURFACE

5. RoHS: COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL: 200.00	 <b>Edmund Optics®</b>		
SHAPE	CONVEX	PLANO	BFL: 177.09			
RADIUS	103.36	$\infty$		TITLE	LARGE PCX CONDENSER LENS 150mm x 200mm	
SURFACE QUALITY	120-80	120-80		DWG NO	67191	SHEET 1 OF 1
CLEAR APERTURE	$\varnothing 145.00$	$\varnothing 145.00$	ALL DIMS IN	mm		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				