


NOTES:



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



1. SUBSTRATE  
COPPER
2. COATING (APPLY ACROSS CLEAR APERTURE)


S1: R(avg) >98% @ 2 - 20µm  
 S2: NONE  
 DAMAGE THRESHOLD, CW: 50kW/cm<sup>2</sup>

3. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SURFACE QUALITY	20-10	N/A
SURFACE ROUGHNESS (Å)	<50 RMS	N/A
SURFACE FLATNESS	λ/20 @ 10.6µm	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

**EO**® Edmund Optics®

TITLE	Ø50mm, IR BROADBAND LASER MIRROR		
DWG NO	33001	SHEET	1 OF 1