





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



CENTER WAVELENGTH CWL (nm)	980
BANDWIDTH (nm)	3.7
OPTICAL DENSITY OD	≥6.0
TRANSMISSION (%)	>90
SURFACE QUALITY	60-40
ANGLE OF INCIDENCE (°)	0 ±2
DURABILITY (ENVIRONMENTAL)	MIL-STD-810F Paragraphs 501.4, 502.4, AND 507.4
DURABILITY (PHYSICAL)	MIL-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, AND 4.5.5.3
OD 5 BLOCKING WAVELENGTH RANGE (nm)	724-970 & 990-1333
OD 6 BLOCKING WAVELENGTH RANGE (nm)	902-965 & 995-1078
RoHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	980nm High Performance Laser Line Filter 12.5mm Dia	
ALL DIMS IN	mm	DWG NO	47496	SHEET 1 OF 1