



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



WAVELENGTH RANGE(nm)	700 - 1100
DIFFUSING ANGLE (°)	12
CLEAR APERTURE CA (mm)	5
FREQUENCY (Hz)	300
POWER SUPPLY	Micro-USB
OPERATING VOLTAGE (V)	5
OPERATING TEMPERATURE (°C)	-20 to 65
STORAGE TEMPERATURE (°C)	-40 to 100

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]



ALL DIMS IN mm

TITLE

12° Diffusion Angle, 5mm CA Laser Speckle Reducer, NIR

DWG NO

88397

SHEET
1 OF 1