## NOTES:

- 1. SUBSTRATE:FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <3 <3 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE): \$1: R(ABS) > 99% @ 1064nm T(ABS) > 95% @ 355nm @ 45° AOI

DAMAGE THRESHOLD (PULSED): 7.5 J/cm² @ 20ns , 20 Hz @ 1064nm 2.5 J/cm² @ 20ns , 20 Hz @ 355nm


S2: R(ABS) < 0.25% @ 355nm @ 45° AOI


DAMAGE THRESHOLD (PULSED): 7.5 J/cm² @ 20ns , 20 Hz @ 355nm




5. ROHS COMPLIANT









SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

|                 | \$1                  | \$2                  |
|-----------------|----------------------|----------------------|
| SHAPE           | PLANO                | PLANO                |
| SURFACE QUALITY | 10-5                 | 10-5                 |
| CLEAR APERTURE  | Ø10.80               | Ø10.80               |
| BEVEL           | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

|                        |    | <b>Edmund Optics</b> |   | S®              |
|------------------------|----|----------------------|---|-----------------|
| THIRD ANGLE PROJECTION |    | TITLE                | Ø12.7mm HS 532, 1064R/355T HARMONIC<br>BEAMSPLITTER |                 |
| ALL DIMS IN            | mm | DWG NO               | 37718   | SHEET<br>1 OF 1 |