

NOTES:



1. SUBSTRATE:
FUSED SILICA
2. S2 TO BE PARALLEL TO S1 TO WITHIN <3ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)
S1: BROADBAND
R(AVG) >98% from 400 - 750nm @ 0 - 45 deg AOI For All Polarizations
R(AVG) >99% from 400-750nm @ 0 - 45 deg AOI For S-Polarization

DAMAGE THRESHOLD,
PULSED: 0.5J/cm², 20ns , 20Hz @ 532nm

S2: NONE



4. FINE GROUND SURFACE

5. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACE
6. SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
7. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div> Edmund Optics®</div></div>					
SHAPE	PLANO	PLANO						
SURFACE QUALITY	20-10	COMMERCIAL POLISH	<div><div>THIRD ANGLE PROJECTION</div><div></div></div>					
SURFACE FLATNESS	λ/10 (BEFORE COATING)	N/A						
CLEAR APERTURE	Ø5.40	N/A	<div><div>ALL DIMS IN</div><div>mm</div></div>					
COATING APERTURE	Ø5.35	N/A						
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	DWG NO		39191		SHEET 1 OF 1	

 **Edmund Optics®**