
NOTES:


- 1. SUBSTRATE: ZnSe
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 3 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE)

\$1& \$2: HIGH- EFFICIENCY BROADBAND (BBAR) $R(AVG) \le 0.5\%$ FROM 8 - $12\mu m$



5. RoHS: COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	40-20	40-20		1		FO 9m
SURFACE FLATNESS @ 10.6µm	λ/20	λ/20	THIRD ANGLE PROJECTION	$\oplus \lhd$	TITLE	50.8m ZnSe W
CLEAR APERTURE	Ø45.72	Ø45.72		 		21100 11
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	39



