NOTES:


1. SUBSTRATE: FLOAT GLASS


2. COATING (APPLY ACROSS CLEAR APERTURE)

\$1 & \$2: BBAR (425-700nm) R(AVG) ≤0.5% @ 425 - 700nm

3. FINE GRIND SURFACE

4. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	80-50	80-50			
CLEAR APERTURE	Ø34.29	Ø34.29			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED			

			Edmund Optics®		
	THIRD ANGLE PROJECTION	\rightarrow	TITLE	38.1mm Dia. x 3mm High Efficiency Window	
_	ALL DIMS IN	mm	DWG NO	39284	SHEET 1 OF 1