



NOTES:

1. VIBRATION RATING:
5 Hz: Vertical = 70-85%, Horizontal = 75-90%
10 Hz: Vertical = 90-97%, Horizontal = 90-97%
2. FEED PRESSURE (psi): 80 (nitrogen or air)
3. CONSTRUCTION:
TOP: STAINLESS STEEL
CORE: ALL STEEL, HIGH DENSITY, CELL-SIZED HONEYCOMB CORE
FRAME: MEDIUM TEXTURE BLACK POWDER COAT
4. WEIGHT: 600 lbs
5. LOAD CAPACITY (lbs):
GROSS: 1400
NET: 350
6. ROHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

<p>THIRD ANGLE PROJECTION</p>	TITLE		750 x 1200mm, LOW PROFILE LAB TABLE	
	ALL DIMS IN	mm	DWG NO	33781
				SHEET 1 OF 1