




NOTES:


1. SUBSTRATE: BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE):  
S1 & S2: R(AVG) < 1.0% @ 700 - 1150nm
3.  FINE GRIND SURFACE
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	4 - 6λ	4 - 6λ
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	Ø4.50	Ø4.50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: 5mm DIA. X 1.75mm THICKNESS, NIR COATED, BOROFLOAT® WINDOW

DWG NO: 12184

SHEET 1 OF 1