



NOTES:

1. SUBSTRATE: FUSED SILICA
2. COATING:  
S1 & S2: NONE
3. CENTERING: < 3 ARCMIN
4. RoHS: COMPLIANT


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	Ø22.86	Ø22.86
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL: 1001.17 mm		 <b>Edmund Optics®</b>	
BFL: 1000.07 mm			
		TITLE	25.4mm Diameter x 1000mm FL, Uncoated, Ultrafast Thin PCX Lens
ALL DIMS IN	mm	DWG NO	11727
			SHEET 1 OF 1