



NOTES:


1. SUBSTRATE: FUSED SILICA
2. COATING:  
S1 & S2: R(ABS) <0.1% @ 700 - 900nm
3. CENTERING: < 3 ARCMIN
4. RoHS: COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	Ø11.43	Ø11.43
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL: 100.12 mm		 <b>Edmund Optics®</b>	
BFL: 99.09 mm			
THIRD ANGLE PROJECTION 		TITLE	12.7mm Diameter x 100mm FL, 700-900nm Coated, Ultrafast Thin PCX Lens
ALL DIMS IN	mm	DWG NO	11654
			SHEET 1 OF 1