




FOCAL LENGTH (EFL): 25 ± 0,25  
BACK FOCAL LENGTH (BFL): 22,31

1 AR COATING: 532nm V-COAT  
R(ABS) < 0,25% @ 532nm @ 0° AOI

| LEFT SURFACE |                          | MATERIAL                   | RIGHT SURFACE |                          |
|--------------|--------------------------|----------------------------|---------------|--------------------------|
| R            | 11,462±0,011 CX          | GLASS FUSED SILICA 458/678 | R             | ∞ PL                     |
| Øe           | 11                       |                            | Øe            | 11                       |
| 3/           | 3 (0,5) λ=632,8 nm       |                            | 3/            | 3 (0,5) λ=632,8 nm       |
| 4/           | -                        |                            | 4/            | 2,18'                    |
| 5/           | 40 - 20 (MIL-PRF-13830B) |                            | 5/            | 40 - 20 (MIL-PRF-13830B) |
| 6/           | -                        |                            | 6/            | -                        |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12mm Dia, x 25mm FL 532nm V-Coat, UV PCX Lens

DWG NO

34088

SHEET SIZE A4

SHEET 1 OF 1