




FOCAL LENGTH (EFL): 12,5 ± 0,13

BACK FOCAL LENGTH (BFL): 10,988

- 1 AR COATING: NIR I
R(AVG) ≤ 0,5% FROM 600-1050nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	9,81±0,01 CX	GLASS N-SF11 785/258	R	∞ PL
Øe	9		Øe	9
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



EO® Edmund Optics®

TITLE

10,0mm Dia, x 12,5mm FL, NIR I, Inked,
Plano-Convex Lens

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

ALL DIMS
IN:

mm

DWG NO

383351NK

SHEET SIZE
A4

SHEET
1 OF 1

INDICATIONS IN ACCORDANCE WITH ISO 10110