





FOCAL LENGTH (EFL): 76,2 ±0,76
 BACK FOCAL LENGTH (BFL): 73,56

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE	
R	39,38±0,039 CX		GLASS N-BK7 517/642	R	∞ PL
Øe	24,4			Øe	24,4
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm
4/	-			4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)
6/	-			6/	-
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	25,4mm Dia, x 76,2mm FL, Uncoated, Plano-Convex Lens
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO	49851
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	SHEET SIZE A4
					SHEET 1 OF 1