



FOCAL LENGTH (EFL): $15 \pm 0,15$
 BACK FOCAL LENGTH (BFL): 13,63

- 1 AR COATING: VIS-NIR
 $R(\text{ABS}) \leq 0,25\%$ AT 880nm @ 0° AOI
 $R(\text{AVG}) \leq 1,25\%$ FROM 400-870nm @ 0° AOI
 $R(\text{AVG}) \leq 1,25\%$ FROM 890-1000nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$6,877 \pm 0,007$ CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 6mm Dia, x 15mm FL VIS-NIR Coated, UV Plano-Convex Lens

DWG NO 63785

SHEET SIZE A4
 SHEET 1 OF 1