


LEFT SURFACE			MATERIAL		RIGHT SURFACE				
R	31,02±0,031 CX		GLASS	N-BK7 517/642	R	∞ PL			
Øe	11				Øe	11			
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm			
4/	-				4/	1,93'			
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)			
6/	-				6/	-			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	[®] Edmund Optics[®]					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	12,0mm Diameter x 60,0mm FL, 532nm V-Coat, PCX Lens				
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	DWG NO	56483	SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110									