




FOCAL LENGTH (EFL):  $12 \pm 0,12$

BACK FOCAL LENGTH (BFL): 10,94

1 AR COATING: 532nm V-COAT  
 $R(ABS) < 0,25\% @ 532nm @ 0^\circ AOI$

| LEFT SURFACE |                            | MATERIAL            | RIGHT SURFACE |                            |
|--------------|----------------------------|---------------------|---------------|----------------------------|
| R            | 6,2±0,006 CX               | GLASS N-BK7 517/642 | R             | ∞ PL                       |
| Øe           | 5,4                        |                     | Øe            | 5,4                        |
| 3/           | 3 (0,5) $\lambda=632,8$ nm |                     | 3/            | 3 (0,5) $\lambda=632,8$ nm |
| 4/           | -                          |                     | 4/            | 1,93'                      |
| 5/           | 40 - 20 (MIL-PRF-13830B)   |                     | 5/            | 40 - 20 (MIL-PRF-13830B)   |
| 6/           | -                          |                     | 6/            | -                          |


PROTECTIVE CHAMFERS AS NEEDED

ROHS:  
COMPLIANT

SCALE:  
NONE

$\lambda = 587,6nm$

FIRST ANGLE  
PROJECTION



**Edmund Optics®**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT  
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE  
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS  
IN:

mm

TITLE

6,0mm Diameter x 12,0mm FL, 532nm  
V-Coat, PCX Lens

DWG NO

65470

SHEET SIZE  
**A4**

SHEET  
1 OF 1