



LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R	9,32±0,009 CX		GLASS	N-BK7 517/642	R	∞ PL	
Øe	8,1				Øe	8,1	
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm	
4/	-				4/	1,93'	
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)	
6/	-				6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	9,0mm Diameter x 18,0mm FL, 1064nm V-Coat, PCX Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO	65535	SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110							
			ALL DIMS IN:	mm			