




FOCAL LENGTH (EFL):  $18 \pm 0,18$   
 BACK FOCAL LENGTH (BFL): 16,22

1 AR COATING: 405nm V-COAT  
 $R(ABS) < 0,25\% @ 405nm @ 0^\circ AOI$

| LEFT SURFACE |                                    | MATERIAL            | RIGHT SURFACE |                                    |
|--------------|------------------------------------|---------------------|---------------|------------------------------------|
| R            | $12,11 \pm 0,012 \text{ CX}$       | GLASS N-SF5 673/322 | R             | $\infty \text{ PL}$                |
| Øe           | 11                                 |                     | Øe            | 11                                 |
| 3/           | 3 (0,5) $\lambda=632,8 \text{ nm}$ |                     | 3/            | 3 (0,5) $\lambda=632,8 \text{ nm}$ |
| 4/           | -                                  |                     | 4/            | 1,49'                              |
| 5/           | 40 - 20 (MIL-PRF-13830B)           |                     | 5/            | 40 - 20 (MIL-PRF-13830B)           |
| 6/           | -                                  |                     | 6/            | -                                  |

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6 \text{ nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12,0mm Diameter x 18,0mm FL, 405nm V-Coat, PCX Lens

DWG NO

66256

SHEET SIZE  
A4

SHEET  
1 OF 1