




FOCAL LENGTH (EFL): 25 ±0,25
 BACK FOCAL LENGTH (BFL): 22,31

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	11,462±0,011 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	11		Øe	11
3/	2 (0,2) λ=632,8 nm		3/	2 (0,2) λ=632,8 nm
4/	-		4/	2,18'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 12mm Diameter x 25mm FL, 266nm Coated, Laser Grade PCX Lens

DWG NO 67940

SHEET SIZE A4

SHEET 1 OF 1