




FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $15,23$

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$8,252 \pm 0,008$ CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	11		Øe	11
3/	2 (0,2) $\lambda=632,8$ nm		3/	2 (0,2) $\lambda=632,8$ nm
4/	-		4/	2,18'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

12mm Diameter x 18mm FL, 532nm
Coated, Laser Grade PCX Lens

DWG NO

67959

SHEET SIZE
A4

SHEET
1 OF 1