




FOCAL LENGTH (EFL): $48 \pm 0,48$
 BACK FOCAL LENGTH (BFL): 46,95

1 AR COATING: 532nm V-COAT
 $R(ABS) < 0,25\% @ 532nm @ 0^\circ AOI$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$24,81 \pm 0,025 CX$	GLASS N-BK7 517/642	R	∞PL
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8 nm$		3/	3 (0,5) $\lambda=632,8 nm$
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6nm$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 6,0mm Diameter x 48,0mm FL, 532nm V-Coat, PCX Lens

DWG NO 69369

SHEET SIZE A4

SHEET 1 OF 1