


LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R	27,91±0,028 CX		GLASS N-BK7 517/642		R	∞ PL		
Øe	8,1				Øe	8,1		
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm		
4/	-				4/	1,93'		
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)		
6/	-				6/	-		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE 9,0mm Diameter x 54,0mm FL, 532nm V-Coat, PCX Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	69375	SHEET SIZE A4	SHEET 1 OF 1