



LEFT SURFACE			MATERIAL		RIGHT SURFACE					
R	258,4±0,258 CX		GLASS N-BK7 517/642		R	∞ PL				
Øe	49				Øe	49				
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm				
4/	-				4/	1,93'				
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)				
6/	-				6/	-				
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm								
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE		50,0mm Diameter x 500,0mm FL, 633nm V-Coat, PCX Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					DWG NO		69464		SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110							ALL DIMS IN:	mm		