



LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R	16,82±0,017 CX		GLASS	N-SF5 673/322	R	∞ PL		
Øe	24				Øe	24		
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm		
4/	-				4/	1,49'		
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)		
6/	-				6/	-		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 	 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	25,0mm Diameter x 25,0mm FL, 980nm V-Coat, PCX Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	DWG NO	69562	SHEET SIZE A4
INDICATIONS IN ACCORDANCE WITH ISO 10110								