




FOCAL LENGTH (EFL): 12 ±0,12  
BACK FOCAL LENGTH (BFL): 9,76

1 AR COATING: 1550nm V-COAT  
R(ABS) < 0,25% @ 1550nm @ 0° AOI

| LEFT SURFACE |                          | MATERIAL             | RIGHT SURFACE |                          |
|--------------|--------------------------|----------------------|---------------|--------------------------|
| R            | 9,42±0,009 CX            | GLASS N-SF11 785/258 | R             | ∞ PL                     |
| Øe           | 11                       |                      | Øe            | 11                       |
| 3/           | 3 (0,5) λ=632,8 nm       |                      | 3/            | 3 (0,5) λ=632,8 nm       |
| 4/           | -                        |                      | 4/            | 1,27'                    |
| 5/           | 40 - 20 (MIL-PRF-13830B) |                      | 5/            | 40 - 20 (MIL-PRF-13830B) |
| 6/           | -                        |                      | 6/            | -                        |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12,0mm Diameter x 12,0mm FL, 1550nm V-Coat, PCX Lens

DWG NO

84239

SHEET SIZE  
A4

SHEET  
1 OF 1