




FOCAL LENGTH (EFL): $-9 \pm 0,09$

BACK FOCAL LENGTH (BFL): $-9,56$

1 AR COATING: VIS 0°
R(AVG) $\leq 0,4\%$ FROM 425-675nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	7,06±0,007 CV	GLASS N-SF11 785/258	R	∞ PL
Øe	2,5		Øe	2,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	3,82'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

3mm Diameter x -9 FL, VIS 0 Coated,
Plano-Concave Lens

DWG NO

84378

SHEET SIZE
A4

SHEET
1 OF 1