




FOCAL LENGTH (EFL): $12 \pm 0,12$
 BACK FOCAL LENGTH (BFL): $10,63$

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$5,5 \pm 0,006$ CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	5,4		Øe	5,4
3/	2 (0,2) $\lambda=632,8$ nm		3/	2 (0,2) $\lambda=632,8$ nm
4/	-		4/	2,18'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

6mm Diameter x 12mm FL, 1064nm
Coated, Laser Grade PCX Lens

DWG NO

87940

SHEET SIZE
A4

SHEET
1 OF 1