




FOCAL LENGTH (EFL): -100 ± 1

BACK FOCAL LENGTH (BFL): -101,37

- 1 AR COATING: UV-AR
 R(ABS) ≤ 1,0% FROM 250-425nm @ 0° AOI
 R(AVG) ≤ 0,75% FROM 250-425nm @ 0° AOI
 R(AVG) ≤ 0,5% FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	45,846±0,046 CV	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12,0mm Dia, x -100 FL, UV-AR Coated, UV Plano-Concave Lens

DWG NO

88037

SHEET SIZE
A4

SHEET
1 OF 1