




FOCAL LENGTH (EFL): 22,5 ± 0,23
 BACK FOCAL LENGTH (BFL): 20,5

- 1 AR COATING: VIS-EXT
 R(AVG) ≤ 0,5% FROM 350-700nm @ 0° AOI
 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	15,12±0,015 CX	GLASS N-SF5 673/322	R	∞ PL
Øe	14		Øe	14
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

15,0mm Dia, x 22,5mm FL, Inked, VIS-EXT Coated Plano-Convex Lens

DWG NO

886961NK

SHEET SIZE
 A4

SHEET
 1 OF 1