




FOCAL LENGTH (EFL): 54 ±0,54

BACK FOCAL LENGTH (BFL): 52,05

- 1 AR COATING: VIS-EXT  
R(AVG) ≤ 0,5% FROM 350-700nm @ 0° AOI
- 2 BLACKENED SURFACE

| LEFT SURFACE |                          | MATERIAL            | RIGHT SURFACE |                          |
|--------------|--------------------------|---------------------|---------------|--------------------------|
| R            | 27,91±0,028 CX           | GLASS N-BK7 517/642 | R             | ∞ PL                     |
| Øe           | 17                       |                     | Øe            | 17                       |
| 3/           | 3 (0,5) λ=632,8 nm       |                     | 3/            | 3 (0,5) λ=632,8 nm       |
| 4/           | -                        |                     | 4/            | 1,93'                    |
| 5/           | 40 - 20 (MIL-PRF-13830B) |                     | 5/            | 40 - 20 (MIL-PRF-13830B) |
| 6/           | -                        |                     | 6/            | -                        |

PROTECTIVE CHAMFERS AS NEEDED

ROHS:  
COMPLIANT

SCALE:  
NONE

λ = 587,6nm

FIRST ANGLE  
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT  
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE  
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS  
IN:

mm



**Edmund Optics®**

TITLE

18,0mm Dia, x 54,0mm FL, VIS-EXT,  
Inked, Plano-Convex Lens

DWG NO

887071NK

SHEET SIZE  
**A4**

SHEET  
1 OF 1