


LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R	206,72±0,207 CX		GLASS	N-BK7 517/642	R	∞ PL	
Øe	39				Øe	39	
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm	
4/	-				4/	1,93'	
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)	
6/	-				6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				40,0mm Dia, x 400,0mm FL, YAG-BBAR Coated Plano-Convex Lens			
INDICATIONS IN ACCORDANCE WITH ISO 10110				DWG NO			
			ALL DIMS IN:	mm	88917		
						SHEET SIZE A4	SHEET 1 OF 1