




FOCAL LENGTH (EFL):  $40 \pm 0,4$   
 BACK FOCAL LENGTH (BFL): 36,77

1 AR COATING: 405nm V-COAT  
 $R(ABS) < 0,25\% @ 405nm @ 0^\circ AOI$

| LEFT SURFACE |                            | MATERIAL            | RIGHT SURFACE |                            |
|--------------|----------------------------|---------------------|---------------|----------------------------|
| R            | $20,67 \pm 0,021$ CX       | GLASS N-BK7 517/642 | R             | $\infty$ PL                |
| Øe           | 19                         |                     | Øe            | 19                         |
| 3/           | 3 (0,5) $\lambda=632,8$ nm |                     | 3/            | 3 (0,5) $\lambda=632,8$ nm |
| 4/           | -                          |                     | 4/            | 1,93'                      |
| 5/           | 40 - 20 (MIL-PRF-13830B)   |                     | 5/            | 40 - 20 (MIL-PRF-13830B)   |
| 6/           | -                          |                     | 6/            | -                          |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6nm$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

20,0mm Diameter x 40,0mm FL, 405nm V-Coat, PCX Lens

DWG NO

88973

SHEET SIZE  
A4

SHEET  
1 OF 1