


LEFT SURFACE			MATERIAL		RIGHT SURFACE	
R	51,68±0,052 CX		GLASS	N-BK7 517/642	R	∞ PL
Øe	19				Øe	19
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm
4/	-				4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)
6/	-				6/	-
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	20,0mm Diameter x 100,0mm FL, 532nm V-Coat, PCX Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO	88995	
INDICATIONS IN ACCORDANCE WITH ISO 10110					ALL DIMS IN:	mm